

Axial/angular expansion joint DN 90

Oper. pressure [bar]: 5

Oper. temp. range [K]: 20 ÷ 310

Oper. travel ranges (max.)

- axial [m] : ± 25
- angular [$^{\circ}$] : ± 6

Weight (max) [Kg] : 3.2

Spring rates (max.)

- axial [N/mm] : 63
- angular [N m/ $^{\circ}$] : 3

Operating fluids : GHe, GN2

Bellows material : AISI 316 L

Application : A5 EPC press. lines

Status : Qualified for flight

