


S410



Cod. →	S410.00012	S410.00014	S410.00016	S410.00018	S410.00020	Description
Descrizione	Compos. <input type="checkbox"/>	Compos. <input type="checkbox"/>	Compos. <input type="checkbox"/>	Compos. <input type="checkbox"/>	Compos. <input type="checkbox"/>	
Appoggi dentati	S110.00001 2	S110.00001 2	S110.00001 2	S110.00001 2	S110.00001 2	Toothed supports
Appoggi dentati	S110.00002 4	S110.00002 4	S110.00002 4	S110.00002 4	S110.00002 4	Toothed supports
Appoggi dentati	S110.00003 2	S110.00003 2	S110.00003 2	S110.00003 2	S110.00003 2	Toothed supports
Staffe semplici	S210.14100 4	S210.14125 4	S210.18125 4	S210.18125 4	S210.22200 4	Flat clamps
Staffe dentate	S220.14100 4	S220.14100 4	S220.18125 4	S220.18125 4	S220.22160 4	Toothed clamps
Viti testa martello	S310.12080 2	S310.14100 2	S310.16100 4	S310.18150 4	S310.20150 4	T-slot bolts
Viti testa martello	S310.12125 4	S310.14150 4	S310.16150 2	S310.18200 2	S310.20200 2	T-slot bolts
Prigionieri completi	S320.10080 2	S320.12080 2	S320.14100 2	S320.16125 2	S320.18125 2	Studs
Prigionieri completi	S320.10100 2	S320.12160 2	S320.14160 2	S320.16160 2	S320.18160 2	Studs
Dadi prolung.	S350.10030 4	S350.12036 4	S350.14042 4	S350.16048 4	S350.18054 4	Extensions nuts
Dadi alti	S340.12018 6	S340.14021 6	S340.16024 6	S340.18027 6	S340.20030 6	Turned toll nuts
Tasselli per cave	S360.10012 4	S360.12014 4	S360.14016 4	S360.16018 4	S360.18020 4	T-slot nuts
Rondelle	S370.00012 6	S370.00014 6	S370.00016 6	S370.00018 6	S370.00020 6	Washers
Peso kg	10,5	12	17	18	27	Weight kg.
Cassetta in legno vuota	S410.BOX01		S410.BOX02		S410.BOX03	Wooden box
Dimensioni	cm. 37 x 32		cm. 47 x 33		cm. 50 x 41	Sizes

N.B. : Si eseguono su richiesta misure non a catalogo

N.B. : Other sizes can be supplied on request

