

## Laboratory and tests

- Fatigue test according to EN ISO 10380
- Burst test
- Measure bench
- Dynamometer
- Aging oven
- Mass spectrometer
- Bending and torsion test
- Non-destructive test (dye-penetrant)
- Acceptance approvals
- Helium leak test: under vacuum with mass spectrometer for detecting  $> 10^{-7}$  mbar l/s (max  $10^{-8}$ ) leakages
- Pressure test: air in water for detecting  $> 10^{-3}$  mbar l/s leakages

