

Technische Dokumentation

Übersicht: Metrische / PG-Ausbrüche

Gewinde	Außen- durchmesser (in mm)	Kern- durchmesser (in mm)
M12 × 1,5	12,0	12,0+0,2
M16 × 1,5	16,0	16,0+0,2
M20 × 1,5	20,0	20,0+0,2
M25 × 1,5	25,0	25,0+0,2
M32 × 1,5	32,0	32,0+0,3
M40 × 1,5	40,0	40,0+0,3
M50 × 1,5	50,0	50,0+0,4
M63 × 1,5	63,0	63,0+0,4
M75 × 1,5	80,0	75,0+0,5
M90 × 2,0	90,0	90,0+0,5

Gewinde	Außen- durchmesser (in mm)	Kern- durchmesser (in mm)
PG 7	12,5	11,28
PG 9	15,2	13,86
PG 11	18,6	17,26
PG 13,5	20,4	19,06
PG 16	22,5	21,16
PG 21	28,3	26,78
PG 29	37,0	35,48
PG 36	47,0	45,48
PG 42	54,0	52,48
PG 48	59,3	57,78